

FS-1000/HTI

PRO FOLLOWSPOT

DISCHARGE LAMP WARNING!

This fixture is fitted with discharge lamps which are highly susceptible to damage if improperly handled. Never touch lamp with bare fingers as the oil from your hands will shorten lamp life. Also, never move fixture until lamp has had ample time to cool. Remember, lamps are not covered under warranty conditions.

Caution! Always disconnect from main power before replacing lamps or servicing unit. Remember to always replace with same lamps and fuses.

Model: FS-1000/HTI

SPECIFICATIONS:

Lamp: ZB-HTI152, 150W discharge

Power: 110V/60Hz

Fuse : 6A GMA

Ventilation: Fan Cooling

Working Position: Any

Weight: 24 lbs.

Size: 9" x 9" x 21"

Warm-up time: 5 minutes



Thank you for purchasing this American DJ® product. For your convenience this lighting effect has been lamped and is ready to be used, there is no assembly required. Please read the following instructions before installing or using your new unit.

Operating Instructions:

Unit is made of extruded aluminum casing, and is ready to be hung or set on a Tripod. After turning on, give the discharge lamp 5 minutes to warm-up to full brightness. The FS-1000/HTI™ features a bright ZB-HTI150, 150W discharge lamp, dual focusing knobs for precise, full focusing, iris control knob at top of unit can also blackout, handle, gel frame, and a hanging bracket. Optional LTS-5 tripod stand comes w/ FS-1000/HTI/Sys system only. The ADJ FS-6C, color changer adapter, which fits on the front of the FS-1000/HTI™, gives the user convenient access to four color gels or to mix colors between the four (FS-6C & Color gels sold separately).

To replace lamp; unscrew screws on the back of the unit, pull out module, replace bulb and reassemble. Do not forget to unplug unit before replacing bulb!

Fuse is located underneath mains input
For service, contact your *American DJ*® dealer.

American DQ®

User Instructions

FS-1000/HTI

PRO FOLLOWSPOT

DISCHARGE LAMP WARNING!

This fixture is fitted with discharge lamps which are highly susceptible to damage if improperly handled. Never touch lamp with bare fingers as the oil from your hands will shorten lamp life. Also, never move fixture until lamp has had ample time to cool. Remember, lamps are not covered under warranty conditions.

Caution! Always disconnect from main power before replacing lamps or servicing unit. Remember to always replace with same lamps and fuses.

Model: FS-1000/HTI

SPECIFICATIONS:

Lamp: ZB-HTI150, 150W discharge

Power: 220V

Fuse : 3A GMA

Ventilation: Fan Cooling

Working Position: Any

Weight: 24 lbs.

Size: 9" x 9" x 21"

Warm-up time: 5 minutes



Thank you for purchasing this American DQ® product. For your convenience this lighting effect has been lamped and is ready to be used, there is no assembly required. Please read the following instructions before installing or using your new unit.

Operating Instructions:

Unit is made of extruded aluminum casing, and is ready to be hung or set on a Tripod. After turning on, give the discharge lamp 5 minutes to warm-up to full brightness. The FS-1000/HTI™ features a bright ZB-HTI150, 150W discharge lamp, dual focusing knobs for precise, full focusing, iris control knob at top of unit can also blackout, handle, gel frame, and a hanging bracket. Optional LTS-5 tripod stand comes w/ FS-1000/HTI/Sys system only. The ADJ FS-6C, color changer adapter, which fits on the front of the FS-1000/HTI™, gives the user convenient access to four color gels or to mix colors between the four (FS-6C & Color gels sold separately).

To replace lamp; unscrew screws on the back of the unit, pull out module, replace bulb and reassemble. Do not forget to unplug unit before replacing bulb!

Fuse is located underneath mains input
For service, contact your *American DQ*® dealer.